

# Connecting cable KEA-1-25P-X

Part number: 177415

FESTO

The cable is available in lengths from 1 to 99 m.



Exemplary representation

## Data sheet

Feature	Value
Mounting type	with through hole
Electrical connection	Plug socket Sub-D 25-pin
Operating voltage range DC	$\leq 250$ V
Operating voltage range AC	$\leq 250$ V
Permissible current load	4 A
Cable diameter	12 mm
Cable structure	25x0,34
Protection class	IP65
Ambient temperature	-20 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
Materials information, cable sheaths	PVC
Materials information, housing	PA
Material information for crimp connectors	Copper alloy Gold plated
Assembly position	Any