


Plug socket with cable KMEB-2-24-M12-0,5-LED

Part number: 177677

FESTO

pre-assembled, for VUVB, MEBH, MOEBH valves and N2 solenoids.



Data sheet

Feature	Value
Switching position indicator	LED
Mounting type	On solenoid valve with M2.5 central screw
Assembly position	Any
Electrical connection	5-pin Plug socket angled Plug pattern type C to EN 175301-803 Per DIN EN 175301-803
Nominal operating voltage DC	24 V
Protective earth connection	Available
Cable length	0.5 m
Cable diameter	4.6 mm
Cable structure	3x0,5
Protection class	IP65 to IEC 60529
Ambient temperature	-5 ... 50 °C
CE symbol (see declaration of conformity)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Material cable sheath	TPE-U(PU)
Cable sheath color	Black
Material housing	PA POM
Housing color	transparent
Material electrical contact	Bronze