

Push-in T-connector CQT-12

Part number: 177687

FESTO



Data sheet

Feature	Value
Nominal width	8.65 mm
Mounting position	Any
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar...7 bar
Temperature-dependent operating pressure	-0.95 bar...15 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
For use in the food industry	See supplementary material information
Ambient temperature	-25 °C...70 °C
Product weight	26 g
No. of outlets	2
No. of supply lines	1
Pneumatic connection 1	For piping system/pneumatic tubing outside diameter of 12 mm
Pneumatic connection 2	for piping system/pneumatic tubing outside diameter of 12 mm
Note on materials	RoHS-compliant
Housing material	POM
Releasing ring material	POM
Material of tube retaining claw	High-alloy stainless steel