

Push-in L-connector CQL-15

Part number: 177692

FESTO



Data sheet

| Feature | Value |
|---|--|
| Nominal width | 12 mm |
| Mounting position | Any |
| Pack size | 1 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.95 bar...7 bar |
| Temperature-dependent operating pressure | -0.95 bar...15 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -25 °C...70 °C |
| Product weight | 20 g |
| Pneumatic connection 1 | For piping system/pneumatic tubing outside diameter of 15 mm |
| Pneumatic connection 2 | for piping system/pneumatic tubing outside diameter of 15 mm |
| Note on materials | RoHS-compliant |
| Housing material | POM |
| Releasing ring material | POM |
| Material of tube retaining claw | High-alloy stainless steel |