


Push-in sleeve CQH-18-QS-16

Part number: 177722

FESTO

to be used as a connection from CQ to QS-fittings.



Data sheet

Feature	Value
Nominal size	11 mm
Assembly position	Any
Container size	1
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 7 bar
Temperature dependent working pressure	-0.95 ... 15 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
Food-safe	See Supplementary material information
Ambient temperature	-25 ... 70 °C
Product weight	8 g
Pneumatic connection, port 1	Push-in sleeve CQ-18
Pneumatic connection, port 2	Push-in sleeve QS-16
Materials note	Conforms to RoHS
Material housing	POM