


Plastic pipe

PQ-PA-12X1,5X3000

Part number: 177728

FESTO

For compressed air, vacuum or liquids. Supplied in lengths of 9ft 9in/3 m.



Data sheet

Feature	Value
Outside diameter	12 mm
Inside diameter	9 mm
Temperature dependent working pressure	-0.95 ... 15 bar
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-25 ... 75 °C
Ambient temperature	-25 ... 75 °C
Product weight according to length	0.051 kg/m
Color	Black
Material tubing	PA