



# Vacuum efficiency valve ISV-M5-CT

Part number: 183520

FESTO

For maintenance of vacuum if one or more suction cups within a group fail to make contact with the workpiece.

Run-out type. Available until 2010.



## Data sheet

Feature	Value
Size	M5
Ejector pulse suitability	8 bar
Assembly position	Any
Working pressure	0 ... 0.95 bar
Required suction rate at -0.5 bar	1 l/min
Operating medium	Atmospheric air
Corrosion resistance classification CRC	2
Ambient temperature	-10 ... 60 °C
Product weight	4 g
Mounting type	Threaded
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Materials information for filter	Sintered steel