

Pressure gauge MA-23-16-R1/8

Part number: 183898

FESTO



Data sheet

Feature	Value
Display range	0 bar...16 bar 0 psi...232 psi
Pressure gauge nominal size	23
Structural design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Inert gas Neutral liquids
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Intermittent load factor	0.6
Measurement accuracy class	4
Degree of protection	IP44
Temperature of medium	-20 °C...60 °C
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	R1/8
Materials in contact with the media	Brass
Material of screwed plug	Brass
Housing material	Brass
Inspection window material	PC
Housing colour	Black
Product weight	27 g
Information on operating and pilot media	No acetylene No oxygen

Feature	Value
Scale	Double scale bar (außen) psi (internal)