


# Socket connector FBSD-GD-13,5

Part number: 18496

FESTO

For field bus connection to valve and valve/sensor manifolds.



## Data sheet

Feature	Value
Based on the standard	EN 61076-2-101 EN 61984
Mounting type	With sleeve nut
Assembly position	Any
Product weight	40 g
Electrical connection	4-pin Straight socket / screw terminal Plug pattern type A to EN 175301-803 M12x1
Operating voltage range DC	≤ 250 V
Operating voltage range AC	≤ 250 V
Acceptable current load at 40°C	4 A
Surge strength	2.5 kV
Cable gland connection	Pg13,5
Permissible cable diameter	10 ... 12 mm
Terminal cross-section	0.75 mm <sup>2</sup>
Protection class	IP67
Ambient temperature	-40 ... 85 °C
CE symbol (see declaration of conformity)	according to EU low voltage guideline
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	1 - Low corrosion stress
Material housing	PA-reinforced
Housing color	Black
Material of union nut	Zinc die-casting Nickel plated
Material electrical contact	Bronze White bronze coated