

Rod clevis CRSG-M27X2

Part number: 185361

FESTO



Data sheet

Feature	Value
Size	M27x2
Mounting position	Any
Based on norm	ISO 8140
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	2022.1 g
Note on materials	RoHS-compliant
Bolt material	High-alloy steel
Clevis material	High-alloy steel
Nut material	High-alloy steel
Fuse material	High-alloy steel