

Plug socket MSSD-ZBZC

Part number: 185521

FESTO



Data sheet

Feature	Value
Maritime classification	See certificate
Type of mounting	On air solenoid valve with self-tapping screw
Mounting position	Any
Product weight	11 g
Electrical connection	Socket
DC operating voltage range	3 V...36 V
Nominal operating voltage DC	24 V
Nominal conductor cross section	0.22 mm ² ...0.34 mm ²
Degree of protection	IP50
Ambient temperature	-10 °C...50 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
Housing material	PA