


Connector block VIGM-03-4,0

Part number: 18652
Product to be discontinued

FESTO

[For valve manifold](#)

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



Data sheet

Feature	Value
Grid dimension	36 mm
Max. number of valve positions	2
Working pressure	-0.9 ... 10 bar
Operating voltage range DC	24 V
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Product weight	300 g
Mounting method for subbase	with internal (female) thread
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 4	G1/8
Materials information for subbase	Aluminum die cast