

Connecting cable KM12-M12-GSGD-5

Part number: 18686

FESTO



Data sheet

Feature	Value
Operating voltage range AC	≤ 60 V
Operating voltage range DC	≤ 75 V
Permissible current load	2.8 A
Protection class	IP67
Ambient temperature with flexible cable installation	-5 ... 70 °C
Ambient temperature	-30 ... 70 °C
Electrical connection	Plug straight / socket straight M12x1 / M12x1 4-pin / 4-pin
Cable structure	4x0,25
Cable length	5 m
Cable sheath color	Grey
Materials information, cable sheaths	PUR