

Axis controller SPC200/P07

Part number: 187815

FESTO

For up to 4 pneumatic axes, with Interbus connection.



Data sheet

Feature	Value
Device setup	Basic unit for 4 plug-in modules Power supply Serial interface Subcontroller Interbus interface
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Continuous shock resistance per DIN/IEC 68, parts 2 - 82	Tested in accordance with severity level 2
Relative air humidity	0 - 95 % non-condensing
Protection class	IP20 to IEC 60529
Vibration resistance per DIN/IEC 68, parts 2 - 6	Tested in accordance with severity level 1
Ambient temperature	-5 ... 50 °C