

Decentralized controller DLP-VSE-3-5/3-G-ASI

Part number: 188473

FESTO

For DLP cylinder series.



Data sheet

| Feature | Value |
|--|---|
| Mounting type | Optional with through hole with accessories |
| Outdoor use | C1 - weather protected locations of use |
| Working pressure | 3 ... 8 bar |
| Nominal working pressure | 6 bar |
| Operating voltage range, DC AS-interface | 26.5 ... 31.6 V |
| Operating voltage range, DC AS-interface, auxiliary power supply | 20.4 ... 28.8 V |
| Max. current consumption | 180 mA |
| CE symbol (see declaration of conformity) | according to EU-EMV guideline |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Corrosion resistance classification CRC | 3 |
| Relative air humidity | 5 - 100 % Condensing |
| Protection class | IP65 in assembled condition to IEC 60529 |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 1,700 g |
| Materials information for cover | Wrought Aluminum alloy Anodized |
| Materials information for seals | NBR |
| Materials information, housing | Wrought Aluminum alloy Anodized |
| Screw material data | Steel Galvanized |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |