

# Round cylinder DSEU-20-25-P-A

Part number: 188561

FESTO

End cap with threaded pins and swivel bearing.  
Type to be discontinued. Available until 2011.



## Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	20 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Variants	Single-ended piston rod
Working pressure	1.5 ... 10 bar
Mode of operation	double-acting
Operating medium	Dried compressed air, lubricated or unlubricated
Corrosion resistance classification CRC	1
Ambient temperature	0 ... 80 °C
Theoretical force at 6 bar, return stroke	158 N
Theoretical force at 6 bar, advance stroke	189 N
Moving mass with 0 mm stroke	31.3 g
Additional weight per 10 mm stroke	7.4 g
Basic weight for 0 mm stroke	107.6 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials note	Contains PWIS substances
Materials information for cover	Wrought Aluminum alloy
Materials information for seals	TPE-U(PU)
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel, non-corrosive