

Suction gripper ESG-150

Part number: 189180

FESTO



Data sheet

| Feature | Value |
|--------------------------------------|--|
| Suction cup diameter | 150 mm |
| Mounting position | Vertical |
| Structural design | Vacuum connection at top Vacuum connection at side with height compensation with long height compensation |
| Classification of suction cup holder | Size 6 |
| Suction cup shape | Round, flat |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -30 °C...200 °C |
| Vacuum connection | G1/4 |
| Note on materials | RoHS-compliant |
| Suction cup material | FPM NBR PUR VMQ (silicone) |