

Vacuum suction cup holder ESH-HB-3-QS

Part number: 189207

FESTO



Data sheet

Feature	Value
Volume	0.519 cm ³
Mounting position	Vertical
Structural design	Vacuum connection at side
Classification of suction cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C...60 °C
Product weight	29 g
Type of mounting	With internal thread
Suction cup mounting	M4
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Seals material	NBR Steel
Retaining bracket material	Aluminum Brass, nickel-plated POM Tempered steel High-alloy steel