

Vacuum suction cup holder ESH-HB-5-G

Part number: 189211

FESTO



Data sheet

Feature	Value
Volume	1.921 cm ³
Mounting position	Vertical
Structural design	Vacuum connection at side
Classification of suction cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	91 g
Type of mounting	With internal thread
Suction cup mounting	M10
Vacuum connection	G1/8
Note on materials	RoHS-compliant
Retaining bracket material	Aluminum Brass, nickel-plated POM Tempered steel High-alloy steel