

Semi-rotary actuator DRE-8-F05-Q08-FO-O

Part number: 190033

FESTO

Single-acting, air connection as per VDI/VDE 3845, Namur valves can be directly flange-mounted



Data sheet

| Feature | Value |
|--|--|
| Size of actuator | 8 |
| Flange hole pattern | F05 |
| Swivel angle | 90 deg |
| End-position adjustment range at 0° | -4 ... 8 deg |
| End-position adjustment range at 90° | -8 ... 4 deg |
| Fitting connection conforms to standard | ISO 5211 |
| Cushioning | No cushioning |
| Assembly position | Any |
| Mode of operation | single-acting |
| Design structure | Rack and pinion |
| Position detection | No |
| Closing direction | Spring force, opening |
| Valve connection conforms to standard | VDI/VDE 3845 (NAMUR) |
| Operating pressure | 2 ... 10 bar |
| ATEX identification | II 2 GD c X |
| ATEX ambient temperature | -20°C ≤ Ta ≤ +60°C |
| Operating medium | Dried compressed air, lubricated or unlubricated |
| CE symbol (see declaration of conformity) | according to EU-Ex protection guideline (ATEX) |
| Corrosion resistance classification CRC | 3 |
| Ambient temperature | -20 ... 80 °C |
| Air consumption at 6 bar per cycle 0°-90°-0° | 2,4 l |
| Product weight | 2,200 g |
| Shaft connection | V14 |
| Pneumatic connection | Subbase G1/4 |
| Materials note | Contains PWIS substances |