



On off valve HE-3-1/4-QS-5/16-U

Part number: 190869

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 3/2, bistable |
| Selection of additional function | with exhaust function |
| Pneumatic connection 1 | 1/4 NPT |
| Pneumatic connection 2 | QS-5/16 |
| Actuation type | Manual |
| Type of mounting | Optionally: Direct mounting via through-hole Direct fastening via thread |
| Standard nominal flow rate | 423.9 l/min |
| Nominal width | 3.5 mm |
| Operating pressure | -0.095 MPa...1 MPa -0.95 bar...10 bar |
| Ambient temperature | 0 °C...60 °C |
| Housing material | PBT-reinforced |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Exhaust air function | Without flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Structural design | Piston gate valve |
| Type of control | Direct |
| Flow direction | Non-reversible |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Class 4 according to ISO 14644-1 |
| Temperature of medium | 0 °C...60 °C |
| Product weight | 36 g |
| Pneumatic connection 3 | Not ducted |
| Material of screwed plug | Brass, nickel-plated |
| Note on materials | RoHS-compliant |
| Seals material | NBR |