

# Vacuum cup without connector ESV-30-SNA

Part number: 190988

FESTO



## Data sheet

Feature	Value
Min. workpiece radius	110 mm
Suction cup diameter	30 mm
Suction cup volume	0.867 cm <sup>3</sup>
Connection position	Top
Mounting position	Any
Special features	Anti-static
Suction cup shape	Round, flat
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Surface resistance	0 Ohm
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
LABS (PWIS) conformity	VDMA24364-A1-L
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	40.8 N
Product weight	2.7 g
Color	Black/white dot
Shore hardness	50 +/- 5
Note on materials	RoHS-compliant
Suction cup material	NBR