

Vacuum suction cup ESV-40-CN

Part number: 191075

FESTO

Wearing part, easily replaceable



Data sheet

Feature	Value
Suction cup height compensator	12.8 mm
Min. workpiece radius	100 mm
suction cup diameter	40 mm
suction cup volume	19.72 cm ³
Position of connection	on top
Assembly position	Any
Suction cup shape	Round, bellows, 3.5 convolutions
Operating pressure MPa	-95 ... 0 kPa
Working pressure	-0.95 ... 0 bar
Operating pressure	-13.775 ... 0 psi
Nominal operating pressure	-70 kPa
Nominal working pressure	-0.7 bar
Nominal operating pressure (psi)	-10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364-A1-L
Food-safe	See Supplementary material information
Ambient temperature	-10 ... 70 °C
Retention force at nominal operating pressure	42.4 N
Product weight	13 g
Color	Black
Shore hardness	50 +/- 5
Materials note	Conforms to RoHS
Material suction cup	NBR