

# Plug socket MSSD-EB-S-M14

Part number: 192745

FESTO



## Data sheet

Feature	Value
Contact durability	10
Type of mounting	On air solenoid valve with M2.5 central screw
Mounting position	Any
Product weight	17 g
Electrical connection	4-pin Socket Form C
Cable diameter	4 mm...6 mm
Nominal conductor cross section	0.25 mm <sup>2</sup> ...0.5 mm <sup>2</sup>
Degree of protection	IP67 as per IEC 60529
Ambient temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA
Housing colour	Black