

# Planar surface gantry EXCH-60-

Part number: 1939785

FESTO



## Data sheet

Feature	Value
Size	60
Mounting position	Vertical Horizontal
Structural design	Planar surface gantry
Operating pressure	8 bar
Max. horizontal acceleration	50 m/s <sup>2</sup>
Max. vertical acceleration	30 m/s <sup>2</sup>
Max. horizontal speed	5 m/s
Max. vertical speed	3 m/s
Repetition accuracy	±0.1 mm
Duty cycle	100%
CE marking (see declaration of conformity)	as per EU machinery directive
UKCA marking (see declaration of conformity)	To UK instructions for machines
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-10 °C...60 °C
Relative air humidity	0 - 90 % Non-condensing
Noise level	81 dB(A)
Degree of protection	IP40
Ambient temperature	10 °C...50 °C
Rated load with maximum dynamic response	6 kg
Type of mounting	With mounting kit With adjusting kit With slot nuts
Note on materials	RoHS-compliant