

# Service unit LFRS-3/4-D-DI-MAXI-KG

Part number: 195202


Classic - do not use for new projects

With lockable regulator head and pressure gauge, for nominal pressure 12 bar, for unlubricated compressed air.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

Type to be discontinued. Available until 2022. See Support Portal for alternative products.

FESTO



## Data sheet

| Feature                                 | Value  |
|---|--|
| Size                                    | Maxi   |
| Series                                  | D  |
| Actuator lock                           | Rotary knob with integrated lock   |
| Assembly position                       | Vertical +/- 5°  |
| Grade of filtration                     | 40 µm  |
| Condensate drain                        | manual rotary  |
| Design structure                        | Branching module<br>Pressure sensor<br>On/off valve<br>Filter regulator with pressure gauge<br>Safety start-up valve |
| Max. condensate volume                  | 43 cm <sup>3</sup>   |
| Bowl guard                              | Metal bowl guard   |
| Pressure gauge                          | with pressure gauge  |
| Working pressure                        | 3 ... 16 bar   |
| Pressure regulation range               | 2.5 ... 12 bar   |
| Standard nominal flow rate              | 3,000 l/min  |
| Operating medium                        | Compressed air in accordance with ISO8573-1:2010 [-:::]<br>Inert gases   |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress  |
| Air purity class at output              | Compressed air in accordance with ISO8573-1:2010 [6:8:4]<br>Inert gases  |
| Medium temperature                      | -10 ... 60 °C  |
| Ambient temperature                     | -10 ... 60 °C  |
| Product weight                          | 5,640 g  |
| Mounting type                           | Line installation<br>with accessories<br>Optional  |
| Pneumatic connection, port 1            | G3/4   |
| Pneumatic connection, port 2            | G3/4   |
| Material housing                        | Zinc die-casting   |
| Material bowl                           | PC   |