


Connector block MHP1-P6-2

Part number: 197198

FESTO

For semi in-line valve MHP1-...-HC/TC



Data sheet

Feature	Value
Max. number of valve positions	6
Working pressure	0 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Mounting method for subbase	with through hole
Mounting method for valve	with internal (female) thread
Pneumatic connection, port 1	M7
Material of connecting plate	Wrought Aluminum alloy