

Electrical plug base MHAP-PI

Part number: 197260

FESTO



Data sheet

Feature	Value
Type of mounting	Clip
Mounting position	Any
Product weight	4 g
Electrical connection	2-pin Socket
DC operating voltage range	60 V
Current rating	3 A
Cable length	0.5 m
Cable diameter	1 mm
Cable design	2 x 0.14 mm ²
Degree of protection	IP40
Ambient temperature	-20 °C...80 °C
Ambient temperature with flexible cable installation	-20 °C...50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	PA
Material of pin contacts	Copper alloy, tin-plated