

Spiral plastic tubing PUN-8X1,25-S-2-BL

Part number: 197594

FESTO

Highly flexible, hydrolysis resistant to a great extent



Data sheet

Feature	Value
Working length	2 m
Outside diameter	8 mm
Block length	0.424 m
Inside diameter	5.7 mm
Coil diameter	60 mm
Number of windings	27
Temperature dependent working pressure	-0.95 ... 10 bar
Authorization	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight	140 g
Pneumatic connection	For push-in connector outside diameter 8 mm for barbed connector internal diameter 6 mm with nut for barbed connector internal diameter 6 mm
Color	blue
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)