

# Duo spiral plastic tubing PUN-8X1,25-S-2-DUO-BS

Part number: 197624

FESTO



## Data sheet

| Feature                                  | Value   |
|--|---|
| Working length                           | 2 m   |
| Outside diameter                         | 8 mm  |
| Block length                             | 0.648 m   |
| Inside diameter                          | 5.7 mm  |
| Winding diameter                         | 60 mm   |
| Number of windings                       | 27  |
| Temperature-dependent operating pressure | -0.95 bar...10 bar  |
| Certification                            | German Technical Control Board (TÜV)  |
| Certificate issuing authority            | B 013277 0506 00  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:-:-]   |
| LABS (PWIS) conformity                   | VDMA24364-B2-L  |
| Ambient temperature                      | -35 °C...60 °C  |
| Product weight                           | 280 g   |
| Pneumatic connection                     | For plug connection outside diameter 8 mm<br>For barbed fitting, inside diameter 6 mm, with union nut<br>For barbed fitting, inside diameter 6 mm |
| Color                                    | Blue/black  |
| Shore hardness                           | D 52 +/-3   |
| Material of pneumatic tubing             | TPE-U(PU)   |