

Duo spiral plastic tubing PUN-12X2-S-2-DUO-BS

Part number: 197630

FESTO



Data sheet

Feature	Value
Working length	2 m
Outside diameter	12 mm
Block length	0.704 m
Inside diameter	8 mm
Winding diameter	95 mm
Number of windings	20
Temperature-dependent operating pressure	-0.95 bar...10 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Product weight	830 g
Pneumatic connection	For plug connection outside diameter 12 mm
Color	Blue/black
Shore hardness	D 52 +/-3
Material of pneumatic tubing	TPE-U(PU)