


Axial kit EAMM-A-P6-38A-40P

Part number: 1983450

FESTO



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	6.5 Nm
Product weight	110 g
Interface code, actuator	P6-38A
Interface code, motor in	40P
Interface code, coupling housing	38A.2
Note on materials	RoHS-compliant