


# Quick coupling plug KS4-N-6

Part number: 2152

FESTO



## Data sheet

Feature	Value
Nominal width	4.5 mm
Operating pressure for entire temperature range	-0.95 bar...12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	15 g
Pneumatic connection 1	N-6
Note on materials	RoHS-compliant