

Parallel kit EAMM-U-86-D60-80P-102

Part number: 2155875

★ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Size	86
Assembly position	Any
Gear unit ratio	1:1
Max. speed	5,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	175 kgmm ²
No-load driving torque	0.25 Nm
Transferable torque	9.5 Nm
Product weight	2,300 g
Interface code, actuator	D60B
Interface code, motor in	80P
Materials note	Conforms to RoHS