

Round cylinder DGS-40-200

Part number: 2477
Product to be discontinued

FESTO

Without end-position cushioning

Type to be discontinued. Available until 2016. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|--|-------------------------|
| Stroke | 200 mm |
| Piston diameter | 40 mm |
| Cushioning | No cushioning |
| Position detection | No |
| Variants | Single-ended piston rod |
| Working pressure | 0.6 ... 10 bar |
| Mode of operation | double-acting |
| Ambient temperature | -20 ... 80 °C |
| Theoretical force at 6 bar, return stroke | 633 N |
| Theoretical force at 6 bar, advance stroke | 754 N |
| Pneumatic connection | G1/4 |