

# Sub-base VABS-S7-BE-B-G14-VDE1

Part number: 2999476

FESTO



## Data sheet

Feature	Value
Mounting position	Any
Pilot air supply port	Internal
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar
Flow rate for piston valve pressurization	2.2 m <sup>3</sup> /h
Flow rate for piston valve exhausting	8.6 m <sup>3</sup> /h
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Product weight	250 g
Type of mounting	With through-hole
Pneumatic connection 1	G1/4
Pneumatic connection 2	VDI/VDE 3845 (NAMUR)
Pneumatic connection 3	G1/4
Note on materials	RoHS-compliant
Material of sub-base	Aluminum, ematal coated
Seals material	NBR