

# Barbed T-connector FCN-3-PK-3/2

Part number: 31314

FESTO



## Data sheet

| Feature   | Value  |
|---|--|
| Nominal width                                   | 1.3 mm   |
| Operating pressure for entire temperature range | -0.95 bar...10 bar   |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7::-]                       |
| Information on operating and pilot media        | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity                          | VDMA24364-B1/B2-L  |
| Ambient temperature                             | 0 °C...60 °C   |
| Pneumatic connection 1                          | for pneumatic tubing outside diameter 3 mm                         |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 4 mm                         |
| Note on materials                               | RoHS-compliant   |
| Housing material                                | Die-cast zinc  |