


Guide unit FEN-40- -KF

Part number: 33485

FESTO

Discontinued, available through 2008



Data sheet

Feature	Value
Size	40
Stroke	10 ... 500 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide
Ambient temperature	-20 ... 80 °C
Displacement force	15 N
Additional weight per 10 mm stroke	32 g
Basic weight for 0 mm stroke	2,370 g
Mounting type	with internal (female) thread
Materials information for guide component	Heat-treatment steel
Materials information, housing	Wrought Aluminum alloy Anodized