


# Foot mounting DAMH-Q12-40

Part number: 3371846

FESTO



## Data sheet

Feature	Value
Size	40
Mounting position	Any
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Max. tightening torque	18 Nm
Product weight	529 g
Type of mounting	With through-hole
Note on materials	RoHS-compliant
Bracket material	Steel, galvanized