


# Pneumatic valve VLX-2-1/2-MS

Part number: 34434

FESTO



## Data sheet

Feature	Value
Structural design	Diaphragm valve
Actuation type	Pneumatic
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	G1/2
Nominal width	13 mm
Valve function	2/2, closed, monostable
Flow direction	Non-reversible
Medium pressure	1 bar...10 bar
Exhaust air function	Without flow control option
Reset method	Pneumatic spring
Type of control	Pilot-controlled
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Medium	Filtered compressed air, 200 µm filter mesh
Temperature of medium	-10 °C...80 °C
Ambient temperature	-10 °C...60 °C
Standard nominal flow rate	4000 l/min
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Housing material	Brass
Material of screws	High-alloy stainless steel
Material number of screw	1.4301
Product weight	450 g