


Pneumatic shock absorber YSR-8-8-C

Part number: 34571

FESTO



Data sheet

Feature	Value
Size	8
Stroke	8 mm
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Max. impact velocity	3 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Single-acting Pushing
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Cushioning length	8 mm
Max. stop force	500 N
Max. energy absorption per stroke	3 J
Max. energy absorption per hour	18000 J
Max. residual energy	0.02 J
Resetting force	2.5 N
Min. insertion force	18 N
Product weight	32 g
Load range	15 kg
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	High-alloy steel
Piston rod material	High-alloy steel