

# Quick coupling plug KS3-1/8-A

Part number: 3492

FESTO



## Data sheet

Feature	Value
Nominal width	4.95 mm
Operating pressure for entire temperature range	-0.95 bar...12 bar
Standard nominal flow rate	563 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Nominal tightening torque	5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	13 g
Pneumatic connection 1	External thread G1/8
Note on materials	RoHS-compliant