

# Pneumatic muffler U-PK-3

Part number: 4646

FESTO



## Data sheet

Feature	Value
Mounting position	Any
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate with respect to atmosphere	310 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	70 dB(A)
Ambient temperature	-10 °C...70 °C
Product weight	4.5 g
Pneumatic connection	PK-3
Cushioning insert material	Bronze
Material of screwed plug	Brass
Note on materials	RoHS-compliant