


control cable KES-SEC-AC-2,5

Part number: 525713

FESTO

Connects the SEC-AC-... motor controller to any desired PLC.



Data sheet

Feature	Value
Cable attribute	Standard
Operating voltage range DC	0 ... 24 V
Protection class	IP20
Note on degree of protection	in assembled condition
Ambient temperature	0 ... 50 °C
Bending radius, flexible cable installation	≥ 220 mm
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Angular
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	25
Electrical connection 1, occupied pins/wires	25
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	26
Electrical connection 2, occupied pins/wires	25
Wire ends	Wire end ferrule
Cable structure	5x(2x0,25)+16x(0,25)
Cable diameter	11 mm
Cable length	2.5 m
Nominal conductor cross-section	0.25 mm ²
Cable identification	Without inscription label holder