

Pressure gauge MA-50-16-R1/4-E-RG

Part number: 525729

FESTO



Data sheet

Feature	Value
Display range	0 bar...16 bar
Conforms to standard	EN 837-1
Pressure gauge nominal size	50
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Inert gas Neutral liquids
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Intermittent load factor	0.66
Measurement accuracy class	2.5
Degree of protection	IP43
Temperature of medium	-20 °C...60 °C
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	R1/4
Materials in contact with the media	Brass
Material of screwed plug	Brass
Housing material	ABS
Inspection window material	PMMA

Feature	Value
Housing colour	Black
Product weight	75 g
Information on operating and pilot media	No acetylene No oxygen
Scale	Single scale bar (außen)