

Branching module MS4N-FRM

Part number: 527704

FESTO



Data sheet

Feature	Value
Mounting position	Any
Structural design	Branching module
Pressure gauge	G1/4 prepared G1/8 prepared with pressure sensor with pressure gauge
Operating pressure	0 bar...14 bar
Standard nominal flow rate in main flow direction 1 -> 2	1200 l/min...4600 l/min
Standard nominal flow rate outlet at top	500 l/min...1600 l/min
Standard nominal flow rate outlet down	500 l/min...1700 l/min
Certification	c UL us - Recognized (OL)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	165 g
Note on materials	RoHS-compliant
Housing material	Die-cast aluminum