

Lubricator MS6-LOE-1/4-U-Z

Part number: 529782

FESTO

Metal bowl, direction of flow: from right to left.



Data sheet

Feature	Value
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	80 cm ³
Bowl guard	integrated as metal shell
Working pressure	1 ... 16 bar
Minimum flow rate for lubricator function	50 l/min
Standard nominal flow rate	2,500 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Medium temperature	0 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 ... 60 °C
Product weight	810 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Conforms to RoHS
Materials information, housing	Aluminum die cast
Materials information for bowl	Wrought Aluminum alloy