


Service unit combination MSB6-3/8-FRC7:J3M1-Z

Part number: 530297

FESTO

Filter-regulator-lubricator combination, 12 bar maximum output pressure, 5 µm filter, with pressure gauge, lockable regulator head, plastic bowl with plastic bowl guard, manual condensate drain, direction of flow: from right to left.



Data sheet

| Feature | Value |
|-----------------------------------------|--------------------------------------------------------------------------------------------------------------|
| Size | 6 |
| Series | MS |
| Actuator lock | Rotary knob with integrated lock |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 5 µm |
| Condensate drain | manual rotary |
| Design structure | Filter regulator with pressure gauge proportional standard mist lubricator |
| Controller function | Output pressure constant with initial pressure compensation with secondary exhaust with return flow |
| Bowl guard | Plastic guard |
| Pressure gauge | with pressure gauge |
| Pressure control range | 0.5 ... 12 bar |
| Inlet pressure 1 | 1.5 ... 20 bar |
| Standard nominal flow rate | 3,400 l/min |
| Operating medium | Compressed air |
| Corrosion resistance classification CRC | 2 |
| Storage temperature | -10 ... 60 °C |
| Air purity class at output | 3.7.- per DIN ISO 8573-1 |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 1,495 g |
| Mounting type | with accessories |
| Pneumatic connection, port 1 | G3/8 |
| Pneumatic connection, port 2 | G3/8 |