

Service unit combination

MSB4-1/4:H7N3M2-WP

Part number: 531089

FESTO

Comprising filter, pressure regulator, lubricator, wall mounting plate.
Maximum output pressure 12 bar, 40 µm filter, with pressure gauge,
metal bowl guard, fully automatic condensate drain, flow direction from
left to right.



Data sheet

Feature	Value
Size	4
Series	MS
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Pressure regulator with gauge Standard filter Standard oil-mist lubricator
Bowl guard	Metal bowl guard
Pressure gauge	with pressure gauge
Working pressure	2 ... 12 bar
Pressure control range	1 ... 12 bar
Standard nominal flow rate	800 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:-]
Medium temperature	-10 ... 60 °C
Mounting type	with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4