

Motor flange EAMF-A-64A/B-87A

Part number: 533140

FESTO

For electromechanical drive with stepper motor



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 ... 60 °C
Product weight	275 g
Interface code, motor in	87A
Interface code, coupling housing	64A 64B
Materials note	Conforms to RoHS